


# **Installation Guide**AWM-A13T

## AWM 130 Arm



# COMPONENT CHECKLIST B C D Screw M4x10mm M4x10mm Screw (x4) A Monitor Arm



### **REQUIRED TOOLS**

• Phillips Head Screwdriver

### **WEIGHT RANGE**

### **Flat Monitor**

0 - 12kg

(0 - 26.5lb)

### **Curved Monitor**

0 - 10kg

(0 - 22lb)

Curved monitors with an overall depth up to 140mm (5.5").


Monitor weight should be within the weight range of all modular elements that make up the complete monitor mounting solution.

### IMPORTANT INFORMATION


(x1)

- ! Please ensure this product is installed as per these installation instructions.
- ! Do not remove or throw away the plastic sleeve on the channel clamp.
- ! The manufacturer accepts no responsibility for incorrect installation.
- ! This product is compatible with Atdec AWM Series Posts and Wall Channels
- ! This product is not suitable for outdoor use or mobile applications
- $! \quad \hbox{Do not over-tighten screws and adjustment points on product}.$
- ! VESA mounted accessories (such as mini PC brackets and mounts), and offset VESA locations, and unevenly weighted monitors (relative to the center of the VESA mounting interface) exert additional leverage that can exceed the capacity of the mount even though the monitor weight may be within the stated range. Please contact Atdec if you would like further information.


### 1. Fix arm to post or wall channel




### 2. Attach VESA head to monitor




### 3. Attach monitor to arm




### 4. Monitor arm cable management



### 5. OPTIONAL Adjust tilt tension



### 6. OPTIONAL Adjust rotation tension



### 7. OPTIONAL Adjust arm joint tension

